

TTRC Copper Closure, unpressurized, gel sealed, 380 mm sheath opening, for up to 100 pair splices



- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensioning mechanism

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Gel sealed closure
Product Series	TTRC

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	4
Cable Sealing Type	Gel filled
Closure Style	In-line
Color	Black
Mounting	Strand
Splicing Capacity, maximum	100

Dimensions

Single Cable Diameter, maximum	19 mm 0.748 in
Single Cable Diameter, minimum	10 mm 0.394 in
Splice Bundle Diameter, maximum	72 mm 2.835 in
Sheath Opening, nominal	380 mm 14.961 in

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

