# FCM-7K0000-192



FDF Fiber Termination Panel, 192 LC/UPC, singlemode, 8 in x 23 in, putty white

### Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FDF

#### **General Specifications**

Functionality	Patching
Application	Used in rear-load FDF-style frames only
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Patch Cord Entry Location	Front, left side   Front, right side
Rack Type	EIA 23 in
Rack Units	4.57
Shelf Movement	Fixed
Total Ports, quantity	192
Dimensions	
Height	203.2 mm   8 in
Width	584.2 mm   23 in
Depth	304.8 mm   12 in
Material Specifications	5
Finish	Powder coated
Material Type	Steel

## Optical Specifications

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 10, 2023



# FCM-7K0000-192

Fiber Mode

Singlemode

#### **Environmental Specifications**

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

### Packaging and Weights

Included

Mounting hardware

Packaging quantity

1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 10, 2023

