## FDP-B4PS22012



CMT Fiber Termination/Splice Panel, 12 FC/UPC, pre-terminated with pigtails, singlemode, 3RU, 19 in, putty white

#### **OBSOLETE**

This product was discontinued on: March 1, 2018

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series CMT

#### General Specifications

Functionality Patching | Splicing

Body StyleSymmetricalColorPutty whiteColor, frontPutty whiteInterface, frontFC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 3

Total Ports, quantity 12

#### **Dimensions**

 Height
 133.35 mm | 5.25 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

### Material Specifications

**Finish** Powder coated

Material Type Steel

COMMSCOPE®

# FDP-B4PS22012

## **Optical Specifications**

**Fiber Mode** Singlemode

#### Packaging and Weights

**Included** Mounting hardware

Packaging quantity 1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

