# FDP-E4PS22072



CMT Fiber Termination/Splice Panel, 72 FC/UPC, pre-terminated with pigtails, singlemode, 7RU, 19 in, putty white

#### OBSOLETE

This product was discontinued on: March 1, 2018

### Product Classification

Regional Availability	Latin America   North America	
Portfolio	CommScope®	
Product Type	Fiber patch/splice panel	
Product Series	CMT	

#### **General Specifications**

Functionality	Patching   Splicing
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Interface, front	FC/UPC
Patch Cord Entry Location	Front, left side   Front, right side
Rack Type	EIA 19 in   EIA 23 in
Rack Units	7
Total Ports, quantity	72
Dimensions	
Height	304.8 mm   12 in
Width	482.6 mm   19 in
Depth	304.8 mm   12 in

## Material Specifications

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 20, 2023



# FDP-E4PS22072

С	in	ic	h
Г		15	

Powder coated

Material Type

Steel

# **Optical Specifications**

Fiber Mode

Singlemode

### Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 20, 2023

