FL2-72RPNL



FL2000 Fiber Termination Panel, unloaded, 72 Ports, 5RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FL2000

General Specifications

Functionality Patching

Color Putty white

Growth Configuration Unloaded

Interface, front Unloaded

Rack Type EIA 19 in

Rack Units 5

Shelf Movement Hinged
Splicing Capacity, maximum 0

Total Ports, quantity 72

Dimensions

 Height
 222.25 mm | 8.75 in

 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications



FL2-72RPNL

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

