

FPX-2FRA08-480



FPX Fiber Optic Termination Module, 2RU, 19in, Singlemode, 48 fiber, LC /UPC Connector, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FPX

General Specifications

Functionality	Patching
Adapter Packs Included, quantity	2
Body Style	Symmetrical
Color	Putty white
Color, front	Putty white
Growth Configuration	Partially loaded
Interface, front	LC/UPC
Patching Capacity, maximum	48
Rack Type	EIA 19 in EIA 23 in
Rack Units	2
Shelf Movement	Sliding
Total Fibers, quantity	48
Total Ports, quantity	48

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in

Ordering Tree

FPX-2FRA08-480

FPX - X X R X X X - X X X

Chassis Size

1	1 RU
2	2 RU
3	3 RU
4	4 RU
5	5 RU

Chassis Style

F	12" depth chassis
---	-------------------

Adapters/Pigtails

0	None
A	Adapter only
P	SM Stranded pigtails and adapters
R	SM Ribbon pigtails and adapters
J	OM4 Stranded pigtails and adapters

Connector/Adapter Color

0	Normal (Green SMAPC, Blue SMUPC, Beige MM)
A	Aqua - (MM OM4)

Connector Type

0	None
7	SC/UPC
J	SC/APC
8	LC/UPC
Z	LC/APC
9	MMSC
6	MMLC

Splice Tray Type

0	None or Adapter only
1	Bare Fusion
2	Health Shrink Fusion
3	Mechanical Fusion (also supports ribbon/mass fusion)

Ports Loaded

00	Base Chassis
12	12
24	24
36	36
48	48
72	72
96	96
144	144
288	288

Density Per Rack Unit by Connector Type

Maximum Density	1	2	3	4	5
LC Connector	48	96	144	192	288
SC Connector	24	48	72	96	144

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included	Mounting hardware
-----------------	-------------------

FPX-2FRA08-480

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

