## FPX-3FR000-000



FPX Fiber Optic Termination/Splice Module, unloaded, 3RU, 19in, putty white

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FPX

#### General Specifications

Functionality Patching | Splicing

**Body Style** Symmetrical

Cable Exit Location Rear, left side | Rear, right side

ColorPutty whiteGrowth ConfigurationUnloadedInterface, frontUnloaded

Rack Type EIA 19 in | EIA 23 in

Rack Units 3

**Shelf Movement** Sliding

Total Fibers, quantity 0

Total Ports, quantity 0

#### Dimensions

 Height
 133.35 mm | 5.25 in


 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

### Ordering Tree



## FPX-3FR000-000



#### Material Specifications

**Finish** Powder coated

Material Type Steel

### **Environmental Specifications**

**Operating Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +85 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +185 \, ^{\circ}\text{F})$ 

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

### Packaging and Weights

**Included** Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications



# FPX-3FR000-000

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

