

K45647-000 | TRAC-AA-17-BOLTED-KITATT

TRAC Copper Closure, unpressurized, gel sealed, 9 inch sheath opening, 17 inch long



- Toolless, extendable and re-enterable closure for freebreathing aerial applications
- Consists of three main components: a central body and two end pieces and self support bond system
- Unique convoluted design provides both mechanical and environmental protection
- Recommended for use on polyethylene insulated cable jackets for straight and branch configurations

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	Latin America North America
Product Type	Gel sealed closure
Product Series	TRAC

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	2
Cable Sealing Type	Gel filled
Closure Style	In-line
Color	Black
Mounting	Strand
Splicing Capacity, maximum	100

Dimensions

Length	431.8 mm 17 in
Single Cable Diameter, maximum	22.86 mm 0.9 in
Splice Bundle Diameter, maximum	50.8 mm 2 in
Sheath Opening, nominal	228.6 mm 9 in

K45647-000 | TRAC-AA-17-BOLTED-KITATT

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

