

SSC-760241465N4 | 12 in Pole Top for Nokia or Samsung



Top of Pole 12in Dia Concealment Enclosure for up to two Airscale Micro radios and/or LAA/CBRS radios or one Samsung LAA or CBRS

- Enclosure for holding 2 Nokia Airscale Micro LAA/CBRS radios
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

-Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your ANDREW Representative for exact model number.

-Mounts directly to ANDREW poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

-Supports (1) "RT4401-48A" or (1) "RT2201-46A" Samsung radio with included adapter bracket. Power Supply to be located in mid pole enclosure.

-Supports AWHQN with separately available kit "860664329-AMK-001"

-Supports DK antenna with separately ordered "MTM106001" bracket.

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Product Classification

Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL DK GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Concrete poles Metal poles Non-tapered poles Tapered poles Wood poles
Radio Compatibility, Nokia	(2) Airscale micro radios (Including LAA & CBRS models) AHIA AHIB AZRB

SSC-760241465N4 | 12 in Pole Top for Nokia or Samsung

Radio Compatibility Samsung RT2201-46A | RT4401-48A

Radios Included None

Dimensions

Height 762 mm | 30 in

Width 304.8 mm | 12 in

Depth 304.8 mm | 12 in

Mounting Bolt Circle Diameter 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.056 m³ | 1.97 ft³

Weight (unloaded) 18.144 kg | 40 lb