

# C240-NMNR

CNT-240 CNT® Jumper with interface types N Male and N Male Right Angle, variable length



## Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-240

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	CNT-240
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Dimensions

Length	0 m   0 ft
Nominal Size	0.240 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.288	18

## Jumper Assembly Sample Label

# C240-NMNR



## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

240BPNM-C-CR	– Type N Male for CNT-240 braided cable
CNT-240	– CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket