### AFGLFSFL1

#### **Base Product**



# Fiber Patch Cord, Singlemode G.657.A2, Grade B, LC/UPC to SC/UPC, Simplex, 1.6 mm LSZH jacket


#### Product Classification

Regional Availability	Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America
Portfolio	CommScope®
Product Type	Fiber patch cord, simplex
Product Series	AFG
General Specifications	
Connector A, quantity	1
Color, connector A	Blue
Connector B, quantity	1
Color, connector B	Blue
Interface, Connector A	LC/UPC
Interface, Connector B	SC/UPC
Total Fibers, quantity	1
Transmission Standards	IEC 61755
Dimensions	
Cable Assembly Length Range (m)	1 – 999
Cable Assembly Length Range (ft)	1 – 999
Diameter Over Jacket	1.6 mm   0.063 in
Ordering Tree	

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



### AFGLFSFL1



### Mechanical Specifications

Minimum Bend Radius, loaded	50 mm   1.969 in
Minimum Bend Radius, unloaded	30 mm   1.181 in
Tensile Load, long term, maximum	33 N   7.419 lbf
Tensile Load, short term, maximum	110 N   24.729 lbf
Cable Crush Resistance, maximum	3.5 N/mm   19.986 lb/in
Mating Durability, maximum	0.2 dB @ 500 cycles

#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®
Performance Grade	IEC Random Mating Grade B
Insertion Loss, maximum, connector A	0.25 dB
Insertion Loss, maximum, connector B	0.25 dB
Return Loss, minimum, connector A	50 dB
Return Loss, minimum, connector B	50 dB

#### **Environmental Specifications**

20 °C to +60 °C (-4 °F to +140 °F)
oual Rated LSZH/Riser

#### Regulatory Compliance/Certifications

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



## AFGLFSFL1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant/Exempted

#### Included Products

460159816	_	Fiber indoor cable, Low Smoke Zero Halogen YL G.657 .A2, 1 fiber, Singlemode G.657.A2, 1.6 mm diameter, Feet jacket marking, Yellow jacket color
860637435 860645407	_	LC/UPC Connector, Singlemode, Blue, Short Boot TeraSPEED® SC/UPC Connector Kit for 2.0 mm Fiber, Singlemode, Blue, Short Boot

#### \* Footnotes

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

