CQHSD | IP6A-12SFTP-PG2S-1LK12

Base Product



3297B Category 7 S/FTP LSZH Preterminated Copper Cable, dual row standard density RJ45 plug to dual row OneLink 2x6, 12 links

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Copper trunk cable assembly

Product Brand GigaSPEED X10D® | InstaPATCH® Cu

General Specifications

ANSI/TIA Category 6A

Cable Type S/FTP (shielded)

Conductor Type Solid

Interface, Connector A RJ45 plug

Interface Feature, connector A Dual row | Standard density

Interface, Connector BOneLink 2x6Interface Feature, connector BStandard

 Link Count
 12

 Wiring
 T568B

Dimensions

Cable Assembly Length Range (m)2-80Cable Assembly Length Range (ft)7-262


Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



CQHSD | IP6A-12SFTP-PG2S-1LK12



Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 °F to +140 °F)}$

Environmental Space Low Smoke Zero Halogen (LSZH)

Flammability Rating UL 94 V-0

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

3297B-4/23 – 3297B Category 7 S/FTP Cable, low smoke zero halogen, 4 pair

count

