

# F1A-HMQM

FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and QMA Male, variable length



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ1-50A

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	QMA Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Dimensions

Length	0 m   0 ft
Nominal Size	1/4 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.04

## Jumper Assembly Sample Label

# F1A-HMQM



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition