UDXLCUC21

Base Product



Ultra Low Loss (ULL) OM4 LC/UPC to Unconnectorized, 1.6 mm Simplex Fiber Pigtail, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber pigtail, jacketed

Product Brand SYSTIMAX ULL

Product Series UDX

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot A Aqua

Color, connector A Beige

Interface, Connector A LC/UPC

Jacket Color Aqua

Dimensions

Total Fibers, quantity


Cable Assembly Length Range (m)1-61Cable Assembly Length Range (ft)2-200

Diameter Over Jacket 1.6 mm | 0.063 in

Ordering Tree



UDXLCUC21



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Plenum

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

760101451 – Fiber indoor cable, LazrSPEED® 1.6 mm Plenum Simplex, Multimode OM4, Feet jacket marking,

P-001-SP-5K-F16AQ Aqua jacket color

860637378 – LazrSPEED® Elite LC Connector duplex for 1.6 mm Fiber, multimode

