


AGX2X2PBF

Base Product



OM4 MPO24 (Pinned) to MPO24 (Unpinned), Fiber Trunk Cable Assembly, 24-Fiber, Method A, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin America | Middle East/Africa | North America

Portfolio

CommScope®

Product Type

Fiber trunk cable assembly

Ordering Note

For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Color, boot A

Red

Color, connector A

Aqua

Color, boot B

Red

Color, connector B

Aqua

Construction Type

Stranded

Furcation Color

Aqua

Interface, Connector A

MPO-24/UPC Male

Interface, Connector B

MPO-24/UPC Female

Jacket Color

Aqua

Polarity

Method A

Fibers per Subunit, quantity

24

Total Fibers, quantity

24

Dimensions

Cable Assembly Length Range (m)

3 – 999

Cable Assembly Length Range (ft)

10 – 999

Ordering Tree

AGX2X2PBF



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

AGX2X2PBF

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760245199 P-024-MP-5K-F30AQ	- Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 24 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color
860662277	- MPO24,FEMALE,OM3/4,AQUA,3.0MM
860662278	- MPO24,MALE,OM3/4,AQUA,3.0MM