



SingleMode SC/APC to SC/APC, InstaPATCH® 360 Ruggedized Fiber Fanout Cable Assembly, 24-Fiber, Low Smoke Zero Halogen (LSZH)

## Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America
Portfolio	CommScope®
Product Type	Ruggedized fanout
Product Brand	SYSTIMAX InstaPATCH® 360
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration   Not available in the United States or Canada

## General Specifications

Color, boot A	Green
Color, boot B	Green
Color, connector A	Green
Color, connector B	Green
Construction Type	Stranded
Fibers per Subunit, quantity	12
Furcation Color	Yellow
Interface, Connector A	SC/APC
Interface, Connector B	SC/APC
Jacket Color	Yellow
Total Fibers, quantity	24

## Dimensions

Cable Assembly Length Range (m)	3 – 305
Cable Assembly Length Range (ft)	8 – 999

## Ordering Tree



## Optical Specifications

**Fiber Type** G.652.D | G.657.A1, TeraSPEED®

## Environmental Specifications

Dual Rated LSZH/Riser | Indoor

## Regulatory Compliance/Certifications

**Classification**

Designed, manufactured and/or distributed under this quality management system

# FNWSASAAF

---

## Included Products

- |                 |   |  |
|-----------------|---|--|
| 460125784       | – | TeraSPEED® SC APC Connector for 1.6 mm Fiber, Duplex, single-mode, green                 |
| N-024-MP-8W-F12 | – | TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 24 fiber with 12 fiber subunits |