

# DFJ-2S320

HELIAX® Discrete, ruggedized, bend insensitive single mode 2 fiber cable, LC to HMFOC



## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	DFJ
Ordering Note	CommScope® non-standard product

## General Specifications


Construction Type	Discrete fiber tail
Interface, Connector A	LC
Interface Body Style, connector A	Straight
Interface, Connector B	HMFOC
Interface Feature, connector B	Outdoor
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	2

## Dimensions

Cable Assembly Length Range (m)	1 – 335
Diameter Over Jacket	5.4 mm   0.213 in

## Ordering Tree

# DFJ-2S320-10M



## Optical Specifications

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.75

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Outdoor

## Packaging and Weights

Cable weight	19 kg/km   12.767 lb/kft
--------------	--------------------------

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted



### \* Footnotes

# DFJ-2S320

---

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)