

C141-KFKF-M35

CF141 Jumper with interface types 4.1/9.5 PM Female and 4.1/9.5 PM Female, 0.35 m



Product Classification

Product Type	Braided cable assembly
Product Series	CF141-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CF141-50
Interface, Connector A	4.3-10 Female
Interface, Connector B	4.3-10 Female
Specification Sheet Revision Level	A

Dimensions

Length	0.35 m 1.148 ft
Nominal Size	0.141 in

Electrical Specifications

3rd Order IMD	-112 dBm
---------------	----------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.119	25.01

Jumper Assembly Sample Label



Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

