

# F2A-HMDR-6M-P

FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Male Right Angle , 6 m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

**Product Type** SureFlex® Premium, static PIM

**Product Series** FSJ2-50

## General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Right angle

**Interface, Connector A** 4.3-10 Male

**Interface, Connector B** 7-16 DIN Male

**Specification Sheet Revision Level** A

## Dimensions

**Length** 6 m | 19.685 ft

**Nominal Size** 3/8 in

## Electrical Specifications

**3rd Order IMD Static** -110 dBm

**3rd Order IMD Static Test Method** Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.1	26.45
1700–2200 MHz	1.1	26.45
2200–2700 MHz	1.1	26.45

## Jumper Assembly Sample Label

# F2A-HMDR-6M-P

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition