



Product Classification

Regional Availability Europe | Middle East/Africa

Portfolio CommScope®

Product Type Fiber pigtail, unjacketed

General Specifications

Connector A, quantity

 Color, boot A
 Blue

 Color, connector A
 Blue

 Interface, Connector A
 LC/UPC

Jacket Color White

Total Fibers, quantity 1

Dimensions

Cord Length 1 m | 3.281 ft

Diameter Over Jacket 0.9 mm | 0.035 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

Insertion Loss, maximum, connector A0.3 dBReturn Loss, minimum, connector A45 dB

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Page 1 of 2

6536880-1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant







