

F4A-PNMDF-1M

FSJ4-50B SureFlex® Jumper with interface types N Male and 7-16 DIN Female, 1 m



Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX® SureFlex®
Product Series	FSJ4-50B

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Female
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
Nominal Size	1/2 in

Electrical Specifications

DTF, Connector A	-32 dB
DTF, Connector B	-32 dB

VSWR/Return Loss

Frequency Band	VSWR, typical	Return Loss, typical (dB)
0–3000 MHz	1.106	25.96
2.2–2.7 GHz	1.083	27.99

Jumper Assembly Sample Label

F4A-PNMDF-1M



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

F4DR-C	- 7-16 DIN Male Right Angle for 1/2 in FSJ4-50B cable
F4NR-HC	- Type N Male Right Angle for 1/2 in FSJ4-50B cable
L4DR-PS	- 7-16 DIN Male Right Angle Positive Stop™ for 1/2 in LDF4-50A cable
L4NR-PS	- Type N Male Right Angle Positive Stop™ for 1/2 in LDF4-50A cable