

F1A-HMNM-7-AT

FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and N Male, AT&T, 7 ft



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® standard

Product Series FSJ1-50A

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 4.3-10 Male

Interface, Connector B N Male

Specification Sheet Revision Level A

Dimensions

Length 2.134 m | 7.001 ft

Nominal Size 1/4 in

Electrical Specifications

3rd Order IMD Dynamic -118 dBm

3rd Order IMD Dynamic Test Method Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.2	21
1700–2700 MHz	1.2	21

Jumper Assembly Sample Label

F1A-HMNM-7-AT



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

