

# F1A-PNFNRM3



FSJ1-50A SureFlex® Jumper with interface types N Female and N Male  
Right Angle, 0.3 m

## Product Classification

Product Type	SureFlex® standard
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ1-50A

## General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	N Female
Interface, Connector B	N Male
Orientation	90°
Specification Sheet Revision Level	A

## Dimensions

Length	0.3 m   0.984 ft
Nominal Size	1/4 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.288	18

## Jumper Assembly Sample Label

# F1A-PNFNR-M3



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

FSJ1-50A	–	FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket
----------	---	--