

# F2A-PNMDR-52N

---

FSJ2-50 SureFlex® Jumper with interface types N Male and 7-16 DIN Male Right Angle, 1.32 m



## Product Classification

**Product Type** SureFlex® standard

**Product Series** FSJ2-50

## General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Right angle

**Interface, Connector A** N Male

**Interface, Connector B** 7-16 DIN Male

**Specification Sheet Revision Level** A

## Dimensions

**Length** 1.32 m | 4.331 ft

**Nominal Size** 3/8 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.29	18

## Jumper Assembly Sample Label

# F2A-PNMDR-52N



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2015 **Classification** Designed, manufactured and/or distributed under this quality management system



## Included Products

- 35422-42 – Heat Treated FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket
- FSJ2-50 – FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket