F4A-HMHM-2M-P

HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 2 m

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® Premium, static PIM

Product Brand HELIAX® | SureFlex®

Product Series RSJ4-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 4.3-10 Male

Interface, Connector B 4.3-10 Male

Specification Sheet Revision Level

Dimensions

Length 2 m | 6.562 ft

Nominal Size 1/2 in

Electrical Specifications

3rd Order IMD Static -119 dBm

3rd Order IMD Static Test MethodTwo +43 dBm carriers per IEC 62037

DTF, Connector A -34 dB

DTF, Connector B -34 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30.04
1700-2200 MHz	1.065	30.04
2200-2700 MHz	1.083	27.99
3400-3800 MHz	1.222	20.01



F4A-HMHM-2M-P

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

