


1-2105061-5



Fiber Optic Patch Cord, Duplex, Multimode, LC/UPC to LC/UPC, LSZH & OFNR, aqua, 15 m

Product Classification

Regional Availability	Asia Australia/New Zealand China India Latin America
Portfolio	CommScope®
Product Type	Fiber patch cord, duplex
Product Series	210

General Specifications


Connector A, quantity	2
Color, boot A	Aqua
Color, connector A	Beige
Connector B, quantity	2
Color, boot B	Aqua
Color, connector B	Beige
Interface, Connector A	LC/UPC
Interface, Connector B	LC/UPC
Jacket Color	Aqua
Total Fibers, quantity	2

Dimensions

Cord Length	15 m 49.213 ft
Diameter Over Jacket	1.8 mm 0.071 in

Ordering Tree

1-2105061-5



Examples of Lengths (meters)	
-5	5 meters
1- -0	10 meters
1- -5	15 meters
7- -5	75 meters
8- -0	80 meters
9- -y	Specific length

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED®
Insertion Loss, maximum, connector A and B	0.3 dB
Insertion Loss, ULL, maximum, connector A and B	0.15 dB

Environmental Specifications

Environmental Space	Dual Rated LSZH/Riser
Qualification Standards	IEC 60332-1 IEC 60332-3 IEC 60754 IEC 61034

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Insertion Loss, maximum, connector A and B Insertion loss is measured at a room temp of +20°C (+68°F)