

F1A-XMPHF-M3



FSJ1-50A SureFlex® Jumper with interface types NEX10 Male Push-Pull and 4.3-10 Female, 0.3 m

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	NEX10 Male
Interface, Connector B	4.3-10 Female
Specification Sheet Revision Level	A

Dimensions

Length	0.3 m 0.984 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.135	23.98
1700–2200 MHz	1.135	23.98
2500–2700 MHz	1.135	23.98
3400–3800 MHz	1.222	20.01
4000–6000 MHz	1.377	15.99

Jumper Assembly Sample Label

F1A-XMPHF-M3



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket