

F1PR-PNMNF-2



HS1RP-50A Jumper with interface types N Female and N Male, 0.61 m

OBSOLETE

This product was discontinued on: March 20, 2017

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX®
Product Series	HS1RP-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Female
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Length	0.61 m 2.001 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.288	18

Jumper Assembly Sample Label

F1PR-PNMNF-2



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

- F1PNF – Type N Female for 1/4 in FSJ1-50A cable
- F1PNM-H – Type N Male for 1/4 in FSJ1-50A cable