

L2-PTMTM-5M-HF

LDF2-50 SureFlex® Jumper with interface types TNC Male and TNC Male, 5M



Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX®
Product Series	LDF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	TNC Male
Interface, Connector B	TNC Male
Specification Sheet Revision Level	A

Dimensions

Length	5 m 16.404 ft
Nominal Size	3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
1000–11000 MHz	1.93	10

Jumper Assembly Sample Label

L2-PTMTM-5M-HF



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- 35422-23 – Heat Treated LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket
- L2TTM-PL – TNC Male Positive Lock for 3/8 in LDF2-50 cable
- LDF2-50 – LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket