

# L4P43-EIA-7M

---

LDF4-50A SureFlex® Jumper with interface type 7/8 in EIA Female Flange, 7 m



## Product Classification

|                       |                                      |
|-----------------------|--------------------------------------|
| <b>Product Type</b>   | Wireless transmission cable assembly |
| <b>Product Brand</b>  | HELIAX®   SureFlex®                  |
| <b>Product Series</b> | LDF4-50A                             |

## General Specifications

|   |                          |
|---|--------------------------|
| <b>Body Style, Connector A</b>            | Straight                 |
| <b>Interface, Connector A</b>             | 7/8 in EIA Female Flange |
| <b>Interface, Connector B</b>             | Sold separately          |
| <b>Specification Sheet Revision Level</b> | A                        |

## Dimensions

|                     |                 |
|---------------------|-----------------|
| <b>Length</b>       | 7 m   22.966 ft |
| <b>Nominal Size</b> | 1/2 in          |

## Electrical Specifications

|                         |        |
|-------------------------|--------|
| <b>DTF, Connector A</b> | -25 dB |
|-------------------------|--------|

## Jumper Assembly Sample Label

# L4P43-EIA-7M



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

- LDF4-50A — LDF4-50A, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket Halogen free jacketing non-fire-retardant (General propose cable for outdoor use only)