

7663274-0005 | ION-U L 18/21-Vac



ION-U® Low Power Remote Unit for DCS 1800 and IMT 2100 Band Applications

OBSOLETE

Product Classification

Product Type	Remote unit
Product Brand	ION-U®

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	Low

Electrical Specifications

Impedance	50 ohm
License Band	DCS 1800 IMT 2100
Voltage Range	85 to 264 Vac

Electrical Specifications, Rx (Uplink)

Operating Frequency Band	1710 – 1785 MHz (DCS 1800) 1920 – 1980 MHz (IMT 2100)
---------------------------------	---

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	1805 – 1880 MHz (DCS 1800) 2110 – 2170 MHz (IMT 2100)
---------------------------------	---