

# 7669582-0008 | ION-U L 7/80-85/17EP/19P-Vdc



ION-U® Low Power Remote Unit for USA 700 and USA 750, SMR 800, CEL 850, AWS 1700, and PCS 1900 Band Applications

**OBSOLETE**

This product was discontinued on: June 30, 2022

## Product Classification

<b>Product Type</b>	Remote unit
<b>Product Brand</b>	ION-U®

## General Specifications

<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Class</b>	Low

## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>License Band</b>	AWS 1700   CEL 850   PCS 1900   SMR 800   USA 700   USA 750
<b>Voltage Range</b>	-60 to -36 Vdc

## Electrical Specifications, Rx (Uplink)

<b>Operating Frequency Band</b>	1710 – 1780 MHz (AWS 1700)   1850 – 1915 MHz (PCS 1900)   699 – 716 MHz (USA 700)   777 – 779 MHz (USA 750)   779 – 787 MHz (USA 700)   817 – 824 MHz (SMR 800)   824 – 849 MHz (CEL 850)
---------------------------------	---

## Electrical Specifications, Tx (Downlink)

<b>Operating Frequency Band</b>	1930 – 1995 MHz (PCS 1900)   2110 – 2180 MHz (AWS 1700)   729 – 746 MHz (USA 700)   746 – 756 MHz (USA 750)   862 – 869 MHz (SMR 800)   869 – 894 MHz (CEL 850)
---------------------------------	---