


DB499-A



1-port sector (yagi) antenna, 806–869 MHz, 60° HPBW, fixed electrical tilt. Mounting pipe diameter, max. 3".

- Rugged, durable design
- Enclosed driven element protects against icing, water penetration, and corrosion
- Unique mounts allow vertical or horizontal polarization

OBSOLETE

This product was discontinued on: **March 31, 2021**

General Specifications

Antenna Type	Sector
Band	Single band
Color	Silver
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radiator Material	Aluminum
RF Connector Interface	N Female
RF Connector Location	Bottom
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Dimensions

Width	152.4 mm 6 in
Depth	25.4 mm 1 in
Length	787.4 mm 31 in
Net Weight, without mounting kit	2.3 kg 5.071 lb

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	806 – 869 MHz
Polarization	Vertical

DB499-A

Electrical Specifications

Frequency Band, MHz	806–869
Gain, dBi	12.1
Beamwidth, Horizontal, degrees	60
Beamwidth, Vertical, degrees	30
Beam Tilt, degrees	0
Front-to-Back Ratio at 180°, dB	15
VSWR Return loss, dB	1.5 14.0
Input Power per Port, maximum, watts	150

Mechanical Specifications

Wind Speed, maximum	201 km/h (125 mph)
----------------------------	--------------------

Packaging and Weights

Included	V-bolts
-----------------	---------

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system




Included Products

11653	–	V-Bolt Mounting Kit for 3 in (76.2 mm) max OD round members. Set of two V-bolts clamp sets.
-------	---	---

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---

11653



V-Bolt Mounting Kit for 3 in (76.2 mm) max OD round members. Set of two V-bolts clamp sets.

Product Classification

Product Type V-bolt mounting kit

General Specifications

Application Outdoor
Color Silver
Compatible 60° Angle 66.04 mm | 2.6 in
Compatible 90° Angle 50.8 mm | 2 in

Dimensions

Compatible Diameter, maximum 76.2 mm | 3 in
Weight, net 0.9 kg | 1.984 lb

Material Specifications

Material Type Galvanized steel | Stainless steel

Packaging and Weights

Included Back straps | Nuts | V-bolts | Washers
Packaging quantity 2

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

