LNXX-MNT-M

Side-By-Side Mounting Kit for 2.4 - 4.5 inch (60 – 115 mm) OD round members. The kit is used with the LNXX-MNT and is the middle mounting bracket when the antennas have three mounting points.

• For LNX 65° models that are 8 feet, the LNXX-MNT-M is used for a center mount along with the LNXX-MNT

OBSOLETE

This product was discontinued on: March 27, 2020

Replaced By:

BSAMNT-SBS-1-2 Side-By-Side Mounting Kit to mount two antennas on a pipe with 2.375 - 4.5 inch (60 – 115 mm)

diameter

Product Classification

Product Type Side mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net5.3 kg | 11.684 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Weight, gross 7.8 kg | 17.196 lb

Regulatory Compliance/Certifications



LNXX-MNT-M

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

BSAMNT-MH – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.



BSAMNT-MH



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum114.3 mm | 4.5 inCompatible Diameter, minimum61 mm | 2.402 inWeight, net4.5 kg | 9.921 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Weight, gross 5.6 kg | 12.346 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





BSAMNT-MH

