

SD-003-KIT1



Static Desiccator Dehydrator, with parallel mounting accessories kit

- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. The compliant desiccant is orange when dry and turns green when saturated

OBSOLETE

This product was discontinued on: September 1, 2023

Product Classification

Product Type Dehydrator

General Specifications

Dehydrator Type Desiccant
Desiccant Capacity 283 liters (10 cu ft) at 80% RH, +20 °C
Mounting Pole
Port Count 1
Port Type 3/8 in PE tube x 1/8 NPT

Dimensions

Product Height 127 mm | 5 in
Product Width 50.8 mm | 2 in
Product Depth 50.8 mm | 2 in
Volume Capacity, maximum 0.028 m³ | 0.999 ft³
Volume Capacity, minimum 0 m³ | 0 ft³

Environmental Specifications

Operating Temperature -29 °C to +49 °C (-20 °F to +120 °F)

Packaging and Weights

SD-003-KIT1

Height, packed	86 mm 3.386 in
Width, packed	165.1 mm 6.5 in
Depth, packed	121.9 mm 4.799 in
Included	90° elbow fitting Brass pipe nipple Instruction sheet Static desiccator
Weight, gross	0.9 kg 1.984 lb
Weight, net	0.2 kg 0.441 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

