

UNA008R

1-port omni antenna, 694–896 MHz, 360° HPBW, 1x RET with manual override. Ships with F-129-S4 mounting kit.

OBSOLETE

This product was discontinued on: March 27, 2020

General Specifications

Antenna Type	Omni
Band	Single band
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Polyester fiberglass pultrusion
Radiator Material	Copper
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Remote Electrical Tilt (RET) Information

RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Power Consumption, idle state, maximum	2 W
Power Consumption, normal conditions, maximum	13 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

Length	2815 mm 110.827 in
Net Weight, without mounting kit	9.8 kg 21.605 lb
Outer Diameter	56 mm 2.205 in

Electrical Specifications

Impedance	50 ohm
------------------	--------

UNA008R

Operating Frequency Band	694 – 896 MHz
Polarization	Vertical

Electrical Specifications

Frequency Band, MHz	694–896
Gain, dBi	8.9
Beamwidth, Horizontal, degrees	360
Beamwidth, Vertical, degrees	9.7
Beam Tilt, degrees	0–8
USLS (First Lobe), dB	15
VSWR Return loss, dB	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150
Input Power per Port, maximum, watts	150

Electrical Specifications, BASTA

Frequency Band, MHz	694–896
Gain by all Beam Tilts, average, dBi	8.6
Gain by all Beam Tilts Tolerance, dB	±0.6
Gain by Beam Tilt, average, dBi	0° 8.6 4° 8.7 8° 8.4
Beamwidth, Vertical Tolerance, degrees	±1.2
USLS, beampeak to 20° above beampeak, dB	15

Mechanical Specifications

Wind Loading @ Velocity, frontal	299.0 N @ 150 km/h (67.2 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	233.0 N @ 150 km/h (52.4 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	299.0 N @ 150 km/h (67.2 lbf @ 150 km/h)
Wind Speed, maximum	250 km/h (155 mph)

Packaging and Weights

Width, packed	300 mm 11.811 in
----------------------	--------------------

UNA008R

Depth, packed	300 mm 11.811 in
Length, packed	3044 mm 119.843 in
Weight, gross	24.8 kg 54.675 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

- F-129-S4 – Fixed Tilt Pipe Mounting Kit for 2.0"-4.5" (50-115mm) OD round members for omni antennas. Includes 2 clamp sets.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance