

Tel-Splice Connector, 3-wire, gel filled, translucent, 100 box/carton



OBSOLETE

This product was discontinued on: August 1, 2016

Replaced By:

CK1830-001
TEL-SPLICE II RF

Tel-Splice II Connector, 3-wire, gel filled, red

Product Classification

Regional Availability

Asia | EMEA | Latin America | North America

Product Type

Splice

Product Series

Tel-Splice

General Specifications

Color

Translucent

Connector Sealant

Gel filled

Dimensions

Compatible Insulated Conductor Diameter, maximum

2.03 mm | 0.08 in

Compatible Conductor Gauge, solid

26-19 AWG

Material Specifications

Contact Plating Material

Tin

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Environmental Space

Outdoor

1-552678-2

Packaging and Weights

Packaging quantity	100
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

