

Tel-Splice Connector, half-tap, dry, clear



OBSOLETE

This product was discontinued on: August 1, 2016

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Splice
Product Series	Tel-Splice

General Specifications

Color	Clear
Connector Sealant	Dry

Dimensions

Compatible Insulated Conductor Diameter, maximum	2.03 mm 0.08 in
Compatible Conductor Gauge, solid	26–19 AWG

Material Specifications

Contact Plating Material	Tin
---------------------------------	-----

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Space	Outdoor

Packaging and Weights

Packaging quantity	100
---------------------------	-----

Packaging Type

Box | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

