

700004310 | MFC-STU-100-BULK-PACK



Pre-Radiused ST II Connector, multimode, 100 bulk pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector

General Specifications

Body Style	Simplex
Color	Black
Ferrule Geometry	Pre-radiused
Interface	ST/UPC

Dimensions

Length	56 mm 2.205 in
Compatible Cable Diameter	0.9 mm 0.035 in 1.6 mm 0.063 in 3 mm 0.118 in

Material Specifications

Ferrule Material	Zirconia
-------------------------	----------

Mechanical Specifications

Cable Retention Strength, maximum	0.50 lb @ 0° 11.24 lb @ 0°
--	------------------------------

Optical Specifications

Fiber Mode	Multimode
Insertion Loss Change, mating	0.2 dB
Optical Components Standard	ANSI/TIA-568-C.3
Insertion Loss Change, temperature	0.1 dB
Insertion Loss, typical	0.3 dB
Return Loss, minimum	20 dB

Packaging and Weights

Packaging quantity	100
---------------------------	-----

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant



* Footnotes

Insertion Loss Change, mating

TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature

Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)