## 760005314 | M81-RCA-110-262-W





M81 RCA to 110 Punchdown Module Audio and Video Adapter, white housing white connector

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Multimedia outlet

General Specifications

ColorWhiteColor, RCAWhiteMountingSnap-inUTP 110 Terminal Block110 ohm

**Electrical Specifications** 

Attenuation dc at Frequency, maximum 2 dB @ 5.5 MHz

Crosstalk @ Gain at Frequency -60 dB @ 5.5 MHz

**Impedance** 75 ohm

**Insulation Resistance, minimum** 50 MOhm

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

#### **Environmental Specifications**

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

**Relative Humidity** 5%–95%, non-condensing

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1



# 760005314 | M81-RCA-110-262-W

### Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



