

D35048-000 | OC-ADP-S5-S5-NNCS

Fiber Optic Simplex Adapter, Multimode SC, beige, with flange

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber adapter
Product Series	OC-ADP

General Specifications

Body Style	Simplex
Color	Aqua
Interface	SC/UPC
Mounting	Square flange
Total Ports, quantity	1
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Material Specifications

Alignment Sleeve Material	Ceramic
----------------------------------	---------

Mechanical Specifications

Coupling Retention Force	70 N 15.737 lbf
---------------------------------	-------------------

Optical Specifications

Fiber Mode	Multimode
Insertion Loss, maximum	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

D35048-000 | OC-ADP-S5-S5-NNCS

Packaging Type

Bag