




1 2 3 4 5 6 7 8 9 10 11 12

A B C D E F G H

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 8000034840: REL TO PRODUCTION PER EAO 606635.	23JAN20 AK	RK/PC



RYYHHTTS4-65A-R7  
SCALE 1:5

**COMMSCOPE, INC. OF NORTH CAROLINA**

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE X ±	2 PLACE .XX ±		
1 PLACE .X ±	ANGLES ±		
FINISH		MATERIAL	
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS INTERPRET PER ISO STANDARDS HANDBOOK TECHNICAL DRAWINGS VOLUMES 1 &amp; 2, THIRD EDITION (2002)</small>		NAME	DATE
		CE AK1095	01/23/2020
		RW AK1095	02/27/2020
		RV RK1074	02/27/2020
		AD KY1009	02/27/2020
RE AC1095	03/04/2020	<b>PRODUCT DRAWING</b> SCALE <b>1:5</b> DOCUMENT NO. <b>RYYHHTTS4-65A-R7-L</b>	
ECN 8000034840-O			
SIZE	WORK AREA	23	MODEL
<b>A2</b>		VERSION	STATUS
		00	RE
DRAWING		VERSION	STATUS
REVISION		A	00
DRAWING		VERSION	STATUS
REVISION		A	RE
			SHEET
			1 OF 1

DENSITY	g/mm <sup>3</sup>
MASS	Kg
VOLUME	mm <sup>3</sup>
SURFACE AREA	mm <sup>2</sup>
HEIGHT	
LENGTH	
WIDTH	

© 2019 CommScope, Inc.

1 2 3 4 5 6 7 8 9 10 11 12