

C240-NMQM

Base Product



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-240

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Cable Family	CNT-240
Interface, Connector A	N Male
Interface, Connector B	QMA Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Length	0 m 0 ft
Nominal Size	0.240 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

Jumper Assembly Sample Label

C240-NMQM



Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

240APNM-CS8	- Type N Male for CNT-240 braided cable
240BPNM-C-CR	- Type N Male for CNT-240 braided cable
240PNM-CS8	- Type N Male for CNT-240 braided cable
240PQMR-C-CR	- QMA Male Right Angle for CNT-240 braided cable
240PQMR-CA	- QMA Male Right Angle for CNT-240 braided cable, for jumpers only not for sale
CNT-240	- CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket
CNT-240-SFR	- CNT-240-SFR, CNT® 50 Ohm Braided Coaxial Cable, black PE jacket