

# 760240957 | 30" Pole Cab with Round Shaft



Bottom of the Pole, 30in Square 4G/5G capable Concealment Enclosure to house and conceal multiple low to high power radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Available with Pole Top concealment, mmWave 5G mounting, luminaire arms.

Available After Market Kits -- ordered separately:

- 860665491-AMK-001 - Ericsson 4480/4415/8863 Radios & 6304 PSU Mounting Kit

## Product Classification

<b>Product Type</b>	Pole cab
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete 6005)   Metallic Silver   Umbra Grey (RAL 7022)
<b>Compatible Foundation Type</b>	Poured Concrete   Pre-Cast Concrete
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WiFi
<b>Cooling</b>	Fan Cooling
<b>Power Supply Compatibility</b>	6302   6304   6308   ABB CC1600   DELTA 2.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	1281   220x   440x   4415   4426   4449   4478   4480   4490   4890   6701   8843   88
<b>Radio Compatibility, Nokia</b>	(2) Airscale dual band radios (160W or 320W and (2) Delta 1kW rectifiers (base)   AHFIA   AHFIB   AHLBBA
<b>Radio Compatibility Samsung</b>	AT1K01   AT1K02   AT1K0X   Diplexer   RF4402D-D1A   RFV01U-D1A   RFV01U-D2A   RT2201-46A 48A
<b>Radios Included</b>	None

## Dimensions

<b>Height Note</b>	4 ft tall Equipment Cabinet Base
<b>Pole Height Options</b>	10.668 m   35 ft   12.192 m   40 ft   6.096 m   20 ft   7.62 m   25 ft   9.144

# 760240957 | 30" Pole Cab with Round Shaft

---

m | 30 ft

**Width** 762 mm | 30 in

**Depth** 762 mm | 30 in

**Depth Note** Square

**Pole Diameter** 203.2 mm | 8 in

## Electrical Specifications

**Input Voltage** 230–115 Vac

**Generator Connection** No connection

**Power/Fiber Input** AC load center with OVP and disconnect

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Steel

## Environmental Specifications

**Thermal Compliance** GR-487