

# 760244794 | VCM-SS-84-12B



Vertical Cable Management Kit, 12in X 84in (305mm X 2134mm) Single Sided, With Door, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Vertical cable management

## General Specifications

<b>Configuration Type</b>	Single-sided
<b>Color</b>	Black
<b>Door, quantity</b>	1

## Dimensions

<b>Height</b>	2,133.6 mm   84 in
<b>Width</b>	304.8 mm   12 in
<b>Depth</b>	279.4 mm   11 in

## Trough Capacity

Ordered Installation - 40%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	492	492	397	397	248	248
8 in	671	671	541	541	338	338
10 in	850	850	685	685	429	429
12 in	1029	1029	829	829	518	518
Randomized Installation - 20%						
VCM Width	Cat 5e		Cat 6		Cat 6A	
	Front Trough	Rear Trough	Front Trough	Rear Trough	Front Trough	Rear Trough
6 in	246	246	198	198	124	124
8 in	335	335	270	270	169	169
10 in	425	425	343	343	214	214
12 in	514	514	415	415	259	259

**Top View of VCM**

Example for 8" VCM Capacity (Randomized Installation - 20%)

## Material Specifications

# 760244794 | VCM-SS-84-12B

---

**Finish** Powder-coated, smooth

**Material Type** Metal

## Environmental Specifications

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Four 1/2-20 hex nuts | Four 1/2-20 x 1 in hex head bolts | Four flat washers | Instruction sheet | Two spools

**Packaging quantity** 1

**Packaging Type** Assembled

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

