FE-12104-T-R4



HELIAX® Fiber and Power Junction Box for 1 Hybrid Trunk / 4 Hybrid Jumper Cables, Blue and Grey Terminal Blocks

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Outdoor junction box

Product Brand HELIAX®

General Specifications

Application Used as a fiber/power junction box

Cable Entry, quantity, maximum, bottom 5

Color Gray

Mounting Pipe, 44–114 mm (1.75–4.5 in) OD | Wall

Dimensions

Height317.5 mm | 12.5 inWidth266.7 mm | 10.5 inDepth101.6 mm | 4 inCable Entry Fiber Gland Size, maximum25 mm | 0.984 inCable Entry Fiber Gland Size, minimum18 mm | 0.709 inCable Entry Jumper Gland Size, maximum18 mm | 0.709 inCable Entry Jumper Gland Size, minimum13 mm | 0.512 in

Material Specifications

Material Type High-impact polycarbonate, UV resistant

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+167 \,^{\circ}\text{F}$)

Environmental Space Indoor | Outdoor

Qualification Standards IEC 60529:2001, IP67



FE-12104-T-R4

Packaging and Weights

Included Mounting kit

Weight, net 1.579 kg | 3.48 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

