

# WP-TH12-B

---



Wood Pole Top Hat, 12 ft 6 in face, 7 in to 14 in wood poles

## Product Classification

**Product Type** Wood pole mount

## General Specifications

**Mounting** Wood pole, 177.8–355.6 mm (7–14 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Height** 355.6 mm | 14 in

**Face Width** 3.81 m | 12.5 ft

**Width** 3810 mm | 150 in

**Length** 914.4 mm | 36 in

**Mounting Diameter, maximum** 355.6 mm | 14 in

**Mounting Diameter, minimum** 177.8 mm | 7 in

**Pipe Outer Diameter** 60.96 mm | 2.4 in

**Stand-off Distance** 914.4 mm | 36 in

**Mounting Circumference, maximum** 353.06 mm | 13.9 in

**Mounting Circumference, minimum** 175.26 mm | 6.9 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact your local ANDREW representative

## Environmental Specifications

**Man Rating** 250 lb vertical man load at 15 mph (BWS)

# WP-TH12-B

---

## Packaging and Weights

<b>Included</b>	Platform   Ring mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	771.016 kg   1,699.8 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

