FGS-HTHR-1/2-30



FiberGuide® Threaded rod, 1/2in Diameter, 30in Length

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Threaded rod

Product Brand FiberGuide®

Product Series FGS

General Specifications

Color Silver

Orientation Horizontal
Section Type Mounting

Dimensions

 Length
 mm | 360 in

 Rod Length
 762 mm | 30 in

Thread Size 1/2 in

Ordering Tree



FGS-HTHR-1/2-30

Rod Diameter

9	1/2	1/2 in
	5/8	5/8 in
	12 MM	12 mm
	14 MM	14 mm
	16 MM	16 mm

^{*} Rod diameter and length needs to be both metric or imperial sized

Rod Length

10	12	12 in
	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

