

# FGS-HTHR-1/2-72

---



FiberGuide® Threaded rod, 1/2in Diameter, 72in Length

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Threaded rod
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Silver
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Mounting

## Dimensions

<b>Length</b>	mm   72 in
<b>Rod Length</b>	1,828.8 mm   72 in
<b>Thread Size</b>	1/2 in

## Ordering Tree

# FGS-HTHR-1/2-72

FGS - HTHR -  $\frac{9}{5/8}$  -  $\frac{10}{72}$

## Rod Diameter

9	1/2	1/2 in
	5/8	5/8 in
	12 MM	12 mm
	14 MM	14 mm
	16 MM	16 mm

## Rod Length

10	12	12 in
	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

\* Rod diameter and length needs to be both metric or imperial sized

## Packaging and Weights

**Weight, net** 1.443 kg | 3.181 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

Compliant

