## FCM-TK/KZD046



FDF Fiber Termination Panel, 144 LC/UPC, singlemode, 8 in x 23 in, putty white, pre-terminated with IFC cable, 46 meters, LC/UPC at far end

#### Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with IFC cable

Product Series FDF

## General Specifications

**Functionality** Patching

**Application** Used in rear-load FDF-style frames only

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type IFC, stranded

**Color** Putty white

**Color, front** Putty white

**Growth Configuration** Fully loaded

Interface, front LC/UPC

**Interface, rear** LC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 23 in

Rack Units 4.57
Shelf Movement Fixed
Total Ports, quantity 144

### **Dimensions**

 Height
 203.2 mm | 8 in

 Width
 584.2 mm | 23 in

 Depth
 304.8 mm | 12 in

**COMMSCOPE®** 

# FCM-TK/KZD046

**Cable Length** 46 m | 150.919 ft

Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

**Environmental Specifications** 

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant

